



- Fully Rated to 13A
- Double Pole Switching
- Safety Shutter System
- Polished Steel Finish
- Black Interior

| Product Specification Data | | Revision Date: 15/10/2021 |
|-------------------------------------|---|---------------------------|
| Product Standard/s | BS 1363-2 | |
| Terminal Capacity L&N | 3 x 1.5, 3 x 2.5, 2 x 4.0 mm ² | |
| Terminal Capacity E | 3 x 1.5, 3 x 2.5, 2 x 4.0 mm ² | |
| Frequency | 50 Hz | |
| CE Conformity | Yes | |
| WEEE Symbol | Yes | |
| G Mark | Yes | |
| UKCA Conformity | Yes | |
| Model | British Standard | |
| Protective contact | No | |
| Number of active pins (round) | 0 | |
| Number of active pins (flat) | 3 | |
| With signal lamp | No | |
| With built-in USB power supply | No | |
| Number of units | 1 | |
| Number of modules (module system) | 0 | |
| Number of socket outlets switchable | 2 | |
| Number of phases | 2 | |
| Imprint/indication | Other | |
| Connection type | Screwed terminal | |
| With hinged lid | No | |
| With enhanced contact protection | Yes | |
| Label space/information surface | Yes | |
| Colour | Chrome | |
| Lockable | No | |
| Insulated mounting | No | |
| With function lighting | No | |
| Fault current protection | No | |
| Special power supply | No special power supply | |

| | |
|---|---------------------------|
| Mounting method | Surface mounted (plaster) |
| Type of fastening | Mounting with screw |
| Material | Metal |
| Material quality | Stainless steel |
| Halogen free | Yes |
| Surface protection | Other |
| Surface finishing | Glossy |
| Anti-bacterial treatment | No |
| With on/off switch | Yes |
| Nominal current | 13 A |
| Nominal voltage | 250 V |
| Suitable for degree of protection (IP) | IP2X |
| Impact strength | IK02 |
| Width of device | 145 mm |
| Height of device | 85 mm |
| Depth of device | 31 mm |
| Min. depth of built-in installation box | 25 mm |

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.